

**Industry Product Group** 

#### CH92

This is advanced information on a new product now in development or undergoing evaluation. Details are subject to change without notice and Cosemitech assumes no obligation for future manufacture of this product. Contact Cosemitech for the latest status

**REV 1.0** 

#### FEATURES and FUNCTIONAL DIAGRAM

- Unipolar respond to a single pole: North (CH92S) or South (CH92T and CH92E), making these products well-suited for shift selectors, wiper end/home position, door ajar/open, and vaneinterrupt systems etc.
- Enhanced sensitivity: will operate from Brp 100 Gauss to Bop 150 Gauss typical with very good temperature-stable and stressresistant, allowing the use of smaller, potentially lower-cost magnets or high robust application
- Subminiature, SOT-23-3L(CH92S) or SOT-89-3L(CH92E) surface mount package supplied on tape and reel allows for a compact design with automated component placement, helping to reduce manufacturing costs
- Small, leaded, flat, TO-92S package (CH92T) allows for a compact PCB layout
- Wide operating voltage range of 3.3V to 30V makes these sensors useable in a wide range of applications
- Built-in reverse voltage capability enhances the protection of the sensor and the circuits with which it is used
- Robust design: will operate up to 150 °C
- RoHS-compliant material meets directive 2002/95

**Function Block Diagram** VDD OUT ESD Clamp Current Hal ESD Amplifier Comparato Sinking Clamp GND  $/\!\!\!/$ Programming Circuit M $/\!\!\!/$ 

# **PACKAGE** TO-92S

#### **APPLICATIONS**

SOT-23 -3L

#### Commercial:

-Door or lid closure detection in appliances

SOT-89-3L

- -Speed and RPM sensing in fitness equipment
- -Flow rate sensing in appliances and water softeners
- -Damper or valve position control in HVAC equipment
- -Printer head position sensing Industrial
- -Flow rate sensing in industrial processes
- -Robotic control (cylinder position monitorina)
- -Float-based fluid level sensing Medical
- -Displacement sensor in hospital beds and medical equipment
- -Medication bin monitor on portable drug carts

#### **DESCRIPTION**

The CH92S, CH92E and CH92T are small, versatile digital Hall-effect devices that are operated by the magnetic field from a permanent magnet or an electromagnet.

This unipolar sensors are designed to meet the requirements of a wide range of potential applications. These economical unipolar sensors are well suited for simple, high-volume, cost-sensitive position and motion sensing applications.

The 3.3Vdc to 30 Vdc supply voltage range allows this device to be used in very wide voltage applications. These sensors are available in two package styles: the CH92S in the subminiature SOT-23-3L surface mount package, the CH92E in the subminiature SOT-89-3L surface mount package, the CH92T is available in the leaded,

flat TO-92-style package.

The CH92S and CH92E are available on tape and reel (CH92S 3000 units per reel, CH92E 1000 units per reel), the CH92T is available in a bulk package (1000 units per bag).

## Cosemi

## Cosemitech

#### CH92

#### **Industry Product Group**

This is advanced information on a new product now in development or undergoing evaluation. Details are subject to change without notice and Cosemitech assumes no obligation for future manufacture of this product. Contact Cosemitech for the latest status.

**REV 1.0** 

#### **Table of Contents**

1. Product Family Members	3
2. Pin Definitions and Descriptions	3
3. Absolute Maximum Ratings	
4. ESD Protections	
5. Function Description	
6. Definition of Switching Function	4
7. Temperature Characterization	4
8. Parameters Specification	5
9. Test Conditions	6
10.Typical Application Circuit	6
11.Typical Output Waveform	6
12. Package Information	7



#### CH92

#### **Industry Product Group**

This is advanced information on a new product now in development or undergoing evaluation. Details are subject to change without notice and Cosemitech assumes no obligation for future manufacture of this product. Contact Cosemitech for the latest status.


**REV 1.0** 

1. Product Family Members


Part Number	Marking ID	Description
CH92SR	CH92	Uni-polar, Open Collector Output, Hall-effect digital sensor IC, SOT-23-3L package, tape and reel packing (3000 units per reel)
СН92ТВ	CH92	Uni-polar, Open Collector Output, Hall-effect digital sensor IC, flat, TO-92S package, bulk packing (1000 units per bag)
CH92ER	CH92	Uni-polar, Open Collector Output, Hall-effect digital sensor IC, SOT-89-3L package, tape and reel packing (1000 units per reel)

#### 2. Pin Definitions and Descriptions


SOT-23-3L(S)	TO-92S(T)	Name	Туре	Function
1	1	VDD	Supply	Supply Voltage pin
2	3	OUT	Output	Open Collector Output pin
3	2	GND	Ground	Ground pin







**TO-92S** 



SOT-89-3L

#### 3. Absolute Maximum Ratings

Parameter	Symbol	Min	Max	Units
Supply Voltage	$V_{DD}$	-	40	V
Reverse Voltage	$V_{RDD}$	-	-40	V
Supply Current	I <sub>DD</sub>	-	20	mA
Output Voltage	V <sub>OUT</sub>	-	40	V
Output Current	louт	-	20	mA
Operating Ambient Temperature	T <sub>A</sub>	-40	150	°C
Storage Temperature	Ts	-50	150	°C
Junction temperature	TJ	-50	165	°C
Magnetic Flux	В	No	Limit	Gauss

Note: Exceeding the absolute maximum ratings may cause permanent damage. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.



#### CH92

Industry Product Group

This is advanced information on a new product now in development or undergoing evaluation. Details are subject to change without notice and Cosemitech assumes no obligation for future manufacture of this product. Contact Cosemitech for the latest status.

**REV 1.0** 

#### 4. ESD Protections

Parameter	Value	Unit
All pins 1)	+/-3000	V
All pins <sup>2)</sup>	+/-200	V
All pins 3)	+/-750	V


- 1) HBM (human body mode, 100pF, 1.5 kohm) according to MIL-STD-883H Method 3015.8
- 2) MM (Machine Mode C=200pF, R=0ô) according to JEDEC EIA/JESD22-A115
- 3) CDM (charged device mode) according to JEDEC EIA/JESD22-C101F

#### 5. Function Description


The CH92S/CH92T/CH92E exhibits unipolar magnetic switching characteristics. Therefore, it requires south or north poles to operate properly.

The device behaves as a unipolar with asymmetric operating and release switching points. This means While the magnetic flux density(B) is larger than operate point (Bop), the output will be turned on (Low), while the magnetic flux density(B) is lower than release point (Brp), then turn off (High).

#### 6. Magnetic Activation



#### 7. Temperature Characteristics





#### CH92

#### **Industry Product Group**

This is advanced information on a new product now in development or undergoing evaluation. Details are subject to change without notice and Cosemitech assumes no obligation for future manufacture of this product. Contact Cosemitech for the latest status.

REV 1.0

## 8. Parameters Specification (At 3.3V to 30V supply, 20mA load, TA= -40 °C to 150 °C except where otherwise specified.)

Symbol	Parameter	Test Condition	Min	Тур.	Max	Units
$V_{DD}$	Supply voltage	-40 °C to 150 °C	3.3	-	30	V
$I_{DD}$	Supply Current	$V_{DD} = 5V$	-	3.5	8	mA
V <sub>DSon</sub>	Output saturation voltage	at 20mA, Gauss >200	-	-	0.4	V
I <sub>OFF</sub>	Output Leakage Current	B<50GS	-	-	10	uA
T <sub>R</sub>	Output rise time	V <sub>DD</sub> =12V at 25 °C C <sub>L</sub> = 20 pF	-	-	1.5	uS
T <sub>F</sub>	Output fall time	V <sub>DD</sub> =12V at 25 °C C <sub>L</sub> = 20 pF	-	-	1.5	uS
R <sub>TH</sub>	Thermal resistance: CH92S (SOT-23-3L) CH92T (TO-92S) CH92E(SOT-89-3L)	-	- - -	303 203 230		°C /W °C/W °C/W
B <sub>OP</sub>	Magnetic operating point	TA=25°C	90	150	220	Gauss
$B_RP$	Magnetic release point	TA=25°C	70	100	150	Gauss
B <sub>HYST</sub>	Magnetic hysteresis window	T <sub>A</sub> =25°C  B <sub>OP</sub> -B <sub>RP</sub>	25	50	75	Gauss
F <sub>SW</sub>	Maximum Switching Frequency				100	KHz
Т	Operating temperature		-40	-	150	°C
Ts	Storage temperature:	-	-40	-	150	°C

#### NOTICE

Bipolar Hall-effect sensor ICs may have an initial output in either the ON or OFF state if powered up with an applied magnetic field in the differential zone (applied magnetic field >Brp and <Bop). Cosemitech recommends allowing 10 µs for output voltage to stabilize after supply voltage has reached 5V.

#### NOTICE

The magnetic field strength (Gauss) required to cause the switch to change state (operate and release) will be as specified in the magnetic characteristics. To test the switch against the specified magnetic characteristics, the switch must be placed in a uniform magnetic field.



#### CH92

#### **Industry Product Group**


This is advanced information on a new product now in development or undergoing evaluation. Details are subject to change without notice and Cosemitech assumes no obligation for future manufacture of this product. Contact Cosemitech for the latest status.

**REV 1.0** 

#### 9. Test Conditions

Note: DUT=Device Under Test


#### **Supply Current**



Note 1 - The supply current lop represents the static supply current. OUT is left open during measurement


Note 2 - The device is put under magnetic field with B<BRP

#### **Output Leakage Current**



Note 1 - The device is put under magnetci field with B<BRP


## Output Saturation Voltage



Note 1 - The output saturation voltage VDSon is measuured at VDD=3.8V and VDD=24V

Note 2 - The device is put under magnetic field with B>Bop


#### **Magenetic Thresholds**




Note 1 - Bop is determined by putting the device under magnetic field swept from  $B_{RPmin}$  up to  $B_{OPmax}$  until the output is switched on.

Note 2 - BRP is determined by putting the device under magnetic field swept from Bopmax down to BRPmin until the output is switched off.

#### 10. Typical Application Circuit



#### 11. Typical Output Waveform (The TO-92S package as an example)





#### CH92


#### **Industry Product Group**


This is advanced information on a new product now in development or undergoing evaluation. Details are subject to change without notice and Cosemitech assumes no obligation for future manufacture of this product. Contact Cosemitech for the latest status.

**REV 1.0** 

## 12. Package Information:

#### PACKAGE DESIGNATOR TO-92S







Comple a l	Dimensions	In Millimeters	Dimensions In Inches		
Symbol	Min.	Max.	Min.	Max.	
Α	1.420	1.620	0.056	0.064	
A1	0.660	0.860	0.026	0.034	
b	0.350	0.480	0.014	0.019	
b1	0.400	0.550	0.016	0.022	
С	0.360	0.510	0.014	0.020	
D	3.900	4.100	0.154	0.161	
D1	2.280	2.680	0.090	0.106	
E	3.050	3.250	0.120	0.128	
е	1.270 TYP.		0.050	TYP.	
e1	2.440	2.640	0.096	0.104	
L	15.100	15.500	0.594	0.610	
θ	45° TYP.		45°	TYP.	



#### CH92


#### **Industry Product Group**


This is advanced information on a new product now in development or undergoing evaluation. Details are subject to change without notice and Cosemitech assumes no obligation for future manufacture of this product. Contact Cosemitech for the latest status.


**REV 1.0** 

#### PACKAGE DESIGNATOR

SOT-23-3L







CL. I	Dimensions In	Millimeters	Dimensions	In Inches
Symbol	Min	Max	Min	Max
Α	1.050	1.250	0.041	0.049
A1	0.000	0.100	0.000	0.004
A2	1.050	1.150	0.041	0.045
b	0.300	0.500	0.012	0.020
C	0.100	0.200	0.004	0.008
D	2.820	3.020	0.111	0.119
E	1.500	1.700	0.059	0.067
E1	2.650	2.950	0.104	0.116
е	0.950(	BSC)	0.037(B	SC)
e1	1.800	2.000	0.071	0.079
L	0.300	0.600	0.012	0.024
θ	0°	8°	0°	8°




#### CH92


#### **Industry Product Group**

This is advanced information on a new product now in development or undergoing evaluation. Details are subject to change without notice and Cosemitech assumes no obligation for future manufacture of this product. Contact Cosemitech for the latest status.

**REV 1.0** 

#### PACKAGE DESIGNATOR SOT-89-3L





Combal	Dimensions	In Millimeters	Dimensions In Inches	
Symbol	Min.	Max.	Min.	Max.
Α	1.400	1.600	0.055	0.063
b	0.320	0.520	0.013	0.020
b1	0.400	0.580	0.016	0.023
С	0.350	0.440	0.014	0.017
D	4.400	4.600	0.173	0.181
D1	1.550	REF.	0.061 REF.	
E	2.300	2.600	0.091	0.102
E1	3.940	4.250	0.155	0.167
е	1.500 TYP.		0.060	TYP.
e1	3.000 TYP.		0.118	TYP.
L	0.900	1.200	0.035	0.047



#### CH92

#### **Industry Product Group**

This is advanced information on a new product now in development or undergoing evaluation. Details are subject to change without notice and Cosemitech assumes no obligation for future manufacture of this product. Contact Cosemitech for the latest status.

**REV 1.0** 

Information furnished is believed to be accurate and reliable. However, Cosemitech assumes no responsibility for the consequences of use of such information nor for any infringement of patents or other rights of third parties which may result from its use. No license is granted by implication or otherwise under any patent or patent rights of Cosemi-tech. Specification mentioned in this publication are subject to change without notice. This publication supersedes and replaces all information previously supplied. Cosemitech products are not authorized for use as critical components in life support devices or systems without express written approval of Cosemitech.

The Cosemitech logo is a registered trademark of Cosemitech